



Key Benefits:

The **Phantom Ultra High-Speed UHS-12 camera line** offers ultra high throughputs, superb sensitivity, and special attention to data management.

◆ Ultra-high throughputs: At full megapixel resolution of 1280 x 800, these cameras achieve, in frames per second (fps):

Phantom v2512: Over 25,000 fps Phantom v1612: Over 16,000 fps Phantom v2012: Over 20,000 fps Phantom v1212: Over 12,000 fps

Superb sensitivity for better picture quality and more lighting flexibility. Using the ISO 12232 SAT method, all models are measured at:

| Monochrome | Color | | |
|-------------------------------------|-----------------------------------|--|--|
| ISO 100,000T, 32,000*D | 10,000T*, 6,400D* | | |
| Adjustable E.I. 32,000D-160,000D | Adjustable E.I. 6,400D-32,000D | | |

The **Exposure Index (E.I.)**, with eight selections, brightens the image by increasing the camera's effective ISO - it's like adding light to the subject. E.I. adjusts the image tone curves in software without affecting the native data.





E.I. 8000 applied

E.I. 40,000 applied

For the most current version visit www.phantomhighspeed.com Subject to change Rev June 2017

Phantom[®] v2512 Phantom[®] v2012 Phantom[®] v1612 Phantom[®] v1212

The world's fastest 1 Mpx high-speed digital camera line also comes with great sensitivity and features.

Key Features:

1 Megapixel sensor (1280 x 800)

25 Gpx/s throughput (v2512)

22 Gpx/s throughput (v2012)

16 Gpx/s throughput (v1612)

12 Gpx/s throughput (v1212)

ISO (ISO 12232 SAT method):
Mono: 32,000D; 100,000T*
Color: 6,400D*; 10,000T*

* Measured according to ISO 12232:2006 method

1µs minimum exposure standard

| Camera | Minimum exposure with FAST option | | | |
|--------|--------------------------------------|--|--|--|
| v2512 | 265 ns | | | |
| v2012 | 290 ns | | | |
| v1612 | 500 ns | | | |
| v1212 | 500 ns | | | |

The FAST option is an export controlled feature

Up to 288GB memory

Phantom CineMag® IV 1TB and 2TB compatible

Sturdy, metal body construction

Made in USA



when it's too fast to see, and too important not to.

v2512, v2012 v1612 & v1212

The standard Capture Cable, which attaches to the Capture Port, provides the following signals:

- Ready, which can be combined with other cameras to provide a "system ready" signal
- Strobe
- Auto-Trigger (a hardware trigger signal supplied by Image-Based Auto-Trigger)
- Pre-trigger/Memgate (a falling edge causes the camera to start acquiring pre-trigger frames and wait for a trigger or in Memgate mode, frames acquired while low are discarded and not saved to memory allowing for selective recording)
- Video Out (NTSC or PAL composite video signal)

The optional Break-out-Box (BoB) connected to the Capture Port provides the following signals:

IRIG-In Strobe
IRIG-Out Auto-Trigger

Video Out Pre-trigger/Memgate

Trigger Ready

Event



Phantom v1212 with CineMag®

Data Storage and Management Focus:

Memory: The cameras can be equipped with **72GB, 144GB, or 288GB** of memory. A camera with 288GB of memory, recording at 10,000 fps at 1280 x 800 can record a single high-speed cine for up to **almost 20 seconds,** and over 7.6 seconds of recording time for a v2512 capturing images at 25Gpx/s. The memory can be segmented into 63 partitions for multiple, shorter cines.

Non-volatile memory: The cameras can securely save data into a 1TB or 2TB Phantom CineMag IV. Save speed is 1GB/s, and 288GB of data can be saved in under 5 minutes. Data on a CineMag can be downloaded via a CineStation or the camera, using 1Gb or 10Gb Ethernet.

10Gb Ethernet: 1Gb and 10Gb Ethernet are standard on the Ultrahigh-speed cameras. The 10Gb Ethernet transfers data at up to 600 MB/second on optimized systems.

Sensor Specifications:

Phantom ultra high-speed cameras are based on a Vision Research designed **custom CMOS sensor with a global electronic shutter,** available in **color or monochrome.** Sensor specifications include:

| Parameter | Specification | Benefit | |
|----------------------|--|---|--|
| Sensor Resolution | 1 Mpx: 1280 x 800 | Widescreen format keeps object in the frame longer | |
| Sensor Size | 35.8mm x 22.4mm | Compatible with F-Mount and EOS lenses at full resolution | |
| Pixel Size | 28 Micron | High light sensitivity | |
| Bit Depth | 12 bits | 4,096 gray levels for optimal image quality | |
| Minimum Exposure | 1 µs standard, up to 265 ns with FAST option Helps eliminate | | |

Camera Control:

Phantom Camera Control (PCC) software: Used for complete setup, control, image processing and download, and includes tracking and motion analysis tools. An SDK that supports Labview and Matlab is also available for integration.

On-Camera Controls: On-camera controls are standard. Connect a video monitor to the camera and use the intuitive user interface to control most common camera settings.

Connectivity:

The Phantom v2512, v2012, v1612 & v1212 are **our most "connected" cameras ever!** On the back panel of the camera you will find: The two HD-SDI ports can act as identical 4:2:2 HD-SDI ports with one port set up to provide an (optional) on-screen display to monitor the on-camera controls and camera operation. Or, they can be configured as a "single" 4:4:4 Dual-Link HD-SDI port.

| BNC Connectors | | 9 | Power Switch | | |
|----------------|---------------------------------------|----|---|--|--|
| 1 | Trigger | 10 | Range Data (input azimuth and elevation data from a tracker) | | |
| 2 | Time Code In (IRIG, SMPTE) | 11 | GPS (input time, location from an external GPS receive | | |
| 3 | I/0 1: Ready | 12 | Remote Control Port | | |
| 4 | I/O 2: F-SYNC | 13 | 1 Gb Ethernet | | |
| 5 | I/O 3: Time Code Out (IRIG, SMPTE) | 14 | 10 Gb Ethernet (copper interface, RJ45 connector) | | |
| 6 | I/O 4: Strobe | 15 | Primary DC Input (20-28VDC) | | |
| 7 | HD-SDI 2 | 16 | Backup DC Power | | |
| 8 | HD-SDI 1 | 17 | Capture Port | | |

Advanced Features:

- **Image-Based Auto-Trigger:** Trigger the camera (or a number of connected cameras) from motion detected within the live image. This makes it possible to catch unpredictable events without manually triggering the camera.
- **Internal Mechanical Shutter:** A black reference is obtained by sampling a perfectly black image. No physical access to the camera is needed.
- **Multi-Cine:** Partition internal memory into segments and make shorter recordings back-to-back without missing any action.
- **Continuous Recording:** Automatically saves a recorded cine to a disk drive on a connected PC immediately after it is recorded then re-arms the camera and waiting for the next cine. A recording can be triggered manually, from an event detection system, or by Image-Based Auto-Trigger. The number of recordings is limited only by the amount of available disk storage.
- **SYNC-to-Trigger:** Attaches the F-SYNC pulse to the trigger frame, for accurate frame comparisons among multiple repeated tests.



Environmental Specs:

Power: 100 - 240 VAC, 280 Watt power supply included

Weight (without lens): 17 lbs, 8 oz. (8.1 Kg)
Operating Temperature: -10 to +50 C

10Gb Ethernet operation: +5 to +50 C
Storage temperature: -20 to +70 C
Humidity: 95% non-condensing
Regulatory: EMI/EMC/ESD
Emissions Tests EN 61326-1/FCC part 15

Immunity Tests EN 61326-1

Random Vibration:

Operational 7.5 Grms, 3 axes,

IAW MIL-STD-202G

Shock:

Operational 5.5G, 11mSec sawtooth, 3 axes, 60 pulses total.

Non-Operational 30G, 11mSec, sawtooth,

3 axes, 60 pulses total

Safety: IEC 60950

when it's too fast to see, and too important not to.

- **PIV features:** Particle Image Velocimetry and similar measurement techniques like Particle Tracking Velocimetry (PTV), Laser Induced Florescence (LIF), and Digital Image Correlation (DIC) require extremely accurate timing and the ability to take images in a very stable and predictable way. The straddle time on the v2512 is 375ns, on the v2012 is 400ns, on the v1612 is 425ns, and on the v1212 is 550ns.
- **Burst Mode:** Many experiments require taking images at precisely the same time during the experiment. Burst mode triggers the camera then takes a burst of images at precise time delays.
- Quiet Fans: Turns the fans off to eliminate vibration.

Phantom v2512, v2012, v1612 & v1212

| RESOLUTION | | | | | |
|------------|-----|---------|---------|---------|---------|
| | | v2512 | v2012 | v1612 | v1212 |
| н | V | Max FPS | Max FPS | Max FPS | Max FPS |
| 1280 | 800 | 25,700 | 22,600 | 16,600 | 12,600 |
| 1280 | 720 | 28,500 | 25,100 | 18,400 | 14,000 |
| 1024 | 800 | 30,500 | 26,900 | 19,700 | 15,000 |
| 1024 | 512 | 47,400 | 41,800 | 30,700 | 23,400 |
| 896 | 800 | 33,700 | 29,800 | 21,800 | 16,600 |
| 768 | 768 | 39,100 | 34,750 | 25,300 | 19,300 |
| 640 | 480 | 70,100 | 62,500 | 45,500 | 34,700 |
| 512 | 512 | 75,600 | 67,800 | 49,100 | 37,500 |
| 512 | 384 | 99,800 | 89,550 | 65,000 | 49,600 |
| 384 | 256 | 171,650 | 115,100 | 112,300 | 85,700 |
| 256 | 256 | 206,300 | 188,500 | 135,400 | 103,500 |
| 256 | 128 | 380,100 | 347,800 | 253,000 | 193,900 |
| 128 | 64 | 663,250 | 651,150 | 538,400 | 415,500 |
| 128 | 32 | 663,250 | 651,150 | 626,850 | 551,700 |
| 128 | 16 | 663,250 | 651,150 | 626,850 | 551,700 |

With the FAST Option (FAST Option is an export controlled feature)

| 128 | 64 | 783,100 | 727,200 | | |
|-----|----|-----------|-----------|---------|---------|
| 256 | 32 | 1,000,000 | 949,400 | 724,100 | |
| 768 | 16 | 1,000,000 | 965,500 | 750,000 | 581,800 |
| 384 | 16 | 1,000,000 | 1,000,000 | 954,500 | 744,100 |
| 128 | 32 | 1,000,000 | 1,000,000 | 840,000 | 653,000 |
| 128 | 16 | 1,000,000 | 1,000,000 | 100,000 | 820,500 |

AMETEK Vision Research's digital high-speed cameras are subject to the export licensing jurisdiction of the Export Administration Regulations. As a result, the export, transfer, or re-export of these cameras to a country embargoed by the United States is strictly prohibited. Likewise, it is prohibited under the Export Administration Regulations to export, transfer, or re-export AMETEK Vision Research's digital high-speed cameras to certain buyers and/or end users.

Customers are also advised that some models of AMETEK Vision Research's digital high-speed cameras may require a license from the U.S. Department of Commerce to be: (1) exported from the United States; (2) transferred to a foreign person in the United States; or (3) re-exported to a third country. Interested parties should contact the U.S. Department of Commerce to determine if an export or a re-export license is required for their specific transaction.

Phantom[®] v2512 Phantom[®] v2012 Phantom[®] v1612 Phantom[®] v1212



v1612 with 2TB CineMag

Vision Research Global Support for wherever you are

Our ultra high-speed camera line is supported by Vision Research's Global Service and Support network offering AMECare Performance Services from multiple sites around the globe. Maximize the value of your Phantom camera with a full menu of professional support services. Learn more about our service and support options at www.phantomhighspeed.com/Support

Focused

Since 1950, Vision Research has been designing, and manufacturing high-speed cameras. Our single focus is to invent, build, and support the most advanced cameras possible.





100 Dey Road Wayne, NJ 07470 USA +1.973.696.4500

www.**phantom**highspeed.com